

CCTM-800 / 1100 / 1400

Assembly Instructions

Metal Condensate Collection Trays



Pump House
Glaisdale Drive East
Nottingham. UK
NG8 4LY
Tel: +44 (0)115 900 5858
Fax: +44 (0)115 929 4468


sales@pumph.co.uk
www.pumph.co.uk



Metal Collection Tray - Assembly Instructions

STEP TO STEP GUIDE TO ASSEMBLY

1




Position the tray hangers to match the width span of the wall bracket. Secure with fixings.

2



Place the tray hangers over the bracket arms.

3



Add the rubber washers (supplied separately with the bracket).

4



Secure with nuts, bolts and washers. Position the drain adaptor towards the back.

5



Place the outdoor unit onto the bracket leaving enough room for air circulation and fix.

WHAT IS IN THE BOX

LIST OF COMPONENTS

Item	Qty.	Description
A	1	Tray
B	2	Tray Hangers
D	4	M8 x 30mm Bolt
E	4	M8 Nut
F	8	M8 Washer
G	1	1/2" BSP Male Drain Adaptor

	Dimensions		
	CCTM-800	CCTM-1100	CCTM-1400
Length	800 mm	1100 mm	1400 mm
Width	400 mm	400 mm	400 mm
Weight	5.27kg	6.93kg	8.26kg